

# Micro Mist Separator

## Series AMD

Series AMD can separate and remove aerosol state oil mist in compressed air and remove carbon or dust of more than 0.01 $\mu$ m. It should be used as prefilter for compressed air in precision instruments or for clean room requirements.

### Model

Model	AMD150	AMD250	AMD350	AMD450	AMD550	AMD650	AMD850
Rated flow (l/min (ANR)) <sup>(1)</sup>	200	500	1000	2000	3500	6000	12000
Port size (Nominal size B)	1/8, 1/4, 3/8	1/4, 3/8, 1/2	3/8, 1/2, 3/4	1/2, 3/4, 1	3/2, 1	1, 1 1/2	1 1/2, 2
Weight (kg)	0.38	0.55	0.9	1.4	2.1	4.2	10.5



Note 1) Max. flow capacity at a pressure of 0.7MPa. It varies depending on operating pressure. Refer to "Flow Characteristics" (p.4.6-9) and figure of "Max. air flow" (p.4.5-8).



P.4.5-14

### Specifications

Fluid	Compressed air
Max. operating pressure	1.0MPa
Min. operating pressure <sup>(1)</sup>	0.05MPa
Proof pressure	1.5MPa
Ambient and fluid temperature	5 to 60°C
Filtration	0.01 $\mu$ m(95% particle size collection)
Oil mist removal rate	Max.0.1mg/m <sup>3</sup> (ANR) <sup>(2)</sup> (At oil saturation of element, less than 0.08ppm)
Element life	2 years or when pressure drop reaches 0.1MPa

Note 1) With N.O. auto drain: 0.15MPa

Note 2) At oil mist removal rate blowing compressor is 30mg/m<sup>3</sup>(ANR)

### Accessories (Options)

Applicable models	AMD150	AMD250	AMD350	AMD450	AMD550	AMD650	AMD850
Bracket assembly (With cap bolt, spring washer)	BM51	BM52	BM53	BM54	BM55	BM56	BM57



\*Please refer to "Precautions" on p.4.5-13.

Symbol



# Micro Mist Separator Series **AMD**

## How to Order

### AMD150 to AMD850

AMD **250** **03** **B** **J**

**Body size**

150	1/8
250	1/4
350	3/8
450	1/2
550	3/4
650	1
850	1 1/2

**Thread**

—	Rc (PT)
F	G (PT)
N	NPT

**Port size**

01	1/8 <sup>B</sup>	06	3/4 <sup>B</sup>
02	1/4 <sup>B</sup>	10	1 <sup>B</sup>
03	3/8 <sup>B</sup>	14	1 1/2 <sup>B</sup>
04	1/2 <sup>B</sup>	20	2 <sup>B</sup>

**Accessories(Options)\***

Symbol	Description
—	None
B	Bracket
C	N.C. auto drain
D	N.O. auto drain

\* Refer to the table below for accessory/option combinations

**Options**

J	Drain guide 1/4B female thread
R	IN → OUT reversal
T	Element service indicator



Please refer to p.4.6-6 regarding "How to Order" of case assembly.

### Table: Accessory/Option combinations

☉ Available   □ Not available   ○ Depending on model

Accessories /Options	Accessories					Options							
	C	D	J	R	T	AMD150	AMD250	AMD350	AMD450	AMD550	AMD650	AMD850	
Accessories	N.C. auto drain	C	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉
	N.O. auto drain	D	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉
Options	Drain guide 1/4B	-J	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉
	IN → OUT reversal	-R	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉
	Element service indicator	-T	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉	☉

## How to Select

Select the model in accordance with the following procedure taking the inlet pressure and max. air flow into consideration.

(Example) Inlet pressure: 0.6MPa

Max. air flow capacity: 5m<sup>3</sup>/min.(ANR)


- ① Select the point of contact A of inlet pressure and max. air flow capacity in the graph.
- ② Select the type whose max. air flow capacity is over that point; AMD650.



Note: Make sure to select a model that has the maximum flow rate line above the obtained intersecting point. With a model that has the maximum flow rate line below the obtained intersecting point, the flow rate will be exceeded, thus leading to a problem such as being unable to satisfy the specifications.

## Max. Air Flow

## Max. Air Flow



HA

ID

AMG

AFF

AM








FQ1

Related products

# Series AMD

**Flow Characteristics**/Select the model taking the max. flow capacity into consideration. ——— Element oil saturation ..... Initial condition


Note) Compressed air over max. flow line in the table below may not meet the specifications of the product. It may cause damage to the element.




# Micro Mist Separator Series AMD

## Construction

AMD150 to AMD650



AMD850



### Component Parts

No.	Description	Material	Note
①	Body	Aluminum die cast	Chrome treatment
②	Housing	Aluminum die cast*	(Epoxy coating on inner surface)
③	Sight glass	Tempered glass	

\*AMD850 is aluminum casting



Note) Sight glass is indicated in the figure above for easy understanding of parts, however mounting position is different. Refer to dimensions on p.4.5-11 and p.4.5-12 for details.

### Replacement Parts

No.	Description	Material	Part No.						
			AMD150	AMD250	AMD350	AMD450	AMD550	AMD650	AMD850
④	Element assembly	Glass fiber NBR	AMD-EL150	AMD-EL250	AMD-EL350	AMD-EL450	AMD-EL550	AMD-EL650	AMD-EL850

\*With gasket and O ring

HA□

ID□

AMG

AFF


AM□

FQ1

Related products


# Series AMD

## Dimensions: AMD150 to AMD650




### Accessories

**D: With auto drain (N.O.)**




**C: With auto drain (N.C.)**




\*N.C. auto drain not available for AM650.

### Options

**J: With drain guide**




**T: With element service indicator**



Model	Port size (Nominal size B)	A	B	C	D	E	F	G	Dimensions with mounting bracket											Element service indicator		
									H	I	J	K	L	M	N	O	P	Q	R	S	T	U
AMD150	1/8, 1/4, 3/8	159	13	100	63	20	63	10	166	56	15	5	9	5.5	35	54	70	26	4.5	1.6	24	37
	1/4, 3/8	172	13	113	76	20	76	10	187	66	20	8	12	6	40	66	84	28	5	2.0	27	37
AMD250	1/2	178	16	119	76	20	76	10	187	66	17	8	12	6	40	66	84	28	5	2.0	27	37
	3/8, 1/2	204	16	145	90	20	90	10	218	80	22	8	14	7	50	80	100	34	5	2.3	32	37
AMD350	3/4	210	19	151	90	20	90	10	218	80	19	8	14	7	50	80	100	34	5	2.3	32	37
	1/2, 3/4	225	19	166	106	20	106	10	241	90	25	10	14	9	55	88	110	50	9	3.2	37	37
AMD450	1	232	22	173	106	20	106	10	241	90	21	10	14	9	55	88	110	50	9	3.2	37	37
	3/4, 1	259	22	200	122	20	122	10	277	100	30	10	16	9	65	102	130	60	10	4.5	39	37
AMD650	1, 1 1/2	311	32	253	160	20	160	10	334	150	40	15	20	11	85	136	180	76	12	4.5	55	37


# Micro Mist Separator Series **AMD**

## Dimensions: AMD850





### Accessory

D: With auto drain (N.O.)  
for AMD850



### Options

T: With element service indicator



Model	Port size (Nominal size B)	A	B	C	D	E	F	G	Dimensions with mounting bracket											
									H	I	J	K	L	M	N	O	P	Q	R	S
AMD850	1 1/2, 2	460.5	42	348	220	57.5	220	10	463.5	180	30	15	24	13	120	184	220	110	18	6

HA

ID

AMG

AFF

AM

FQ1

Related products



## Precautions

Be sure to read before handling.  
Refer to p.0-26 and 0-27 for Safety Instructions and common precautions on the products mentioned in this catalogue, and refer to p.4.0-5 to 4.0-7 for precautions on every series.

### Design



## Caution

- ① Design the layout so that the mist separator is installed in an area that is less susceptible to pulsations. The element could be damaged if the difference in internal and external pressures exceeds 0.1MPa.
- ② When using the auto drain, connect the drain piping in the following range:  
Normally closed (N.C.) } .....  
Normally open (N.O.) } .....  
Because tube fittings are provided, use a tube with a bore of 10mm, and keep the overall pipe length within 5m.  
AM850 type (N.O) .....  
Use a tube with a bore of 9mm or more, and keep the overall pipe length within 2.8m.  
If the normally open (N.O.) auto drain is used, because it is designed so that the valve will not open unless the air pressure is 0.15MPa or higher, air could continue to blow out of the drainage discharge area if an air compressor with a small air discharge volume is used. Therefore, when using a compressor that is smaller than 3.7kW, make sure to use the normally closed (N.C.) auto drain.
- ③ The bracket that is provided with the product is for supporting the product itself. Thus, it cannot support the piping or other items that are connected. If these items need to be supported, provide an additional support.

### Mounting



## Caution

- ① Verify the direction of the flow of the compressed air and the "▷" mark that indicates the inlet of the product before connecting. It cannot be used if connected in the opposite direction.
- ② Make sure to install this product on horizontal piping. If it is installed diagonally, laterally, or upside down, the drainage that is separated by the element will splash to the secondary side.

### Maintenance check



## Caution

- ① The replacement interval for the element for models AMD150 to AMD850 is when the pressure drop reaches 0.1MPa or after 2 years of operation, whichever comes first. A pressure drop can be verified with the type with a clogging checker (-T) or with the type with a pressure differential gauge (Made to Order).
- ② When the element has reached its replacement interval, replace it immediately with a new element. Replace the O ring, the gasket, and the element with new parts.
- ③ When using models AMD150 to AMD850 with a drain valve, drain guide, or a ball valve, discard the drainage before the drainage level reaches the center of the sight glass. If the drainage is not discarded properly, it will flow to the secondary side.

# Series AMD

# Made to Order Specifications

Please contact SMC for detailed specifications, dimensions or delivery.




## ① With Pressure Differential Gauge (GD40-2-01)

A pressure differential gauge can be installed in the body to check the life of the filter element. It allows for easier piping and compact size.


### Specification

Applicable model	AMD150 to AMD850
------------------	------------------

**How to Order** \*Refer to "How to Order" for standard type (p.4.5-8).



### Dimensions



Model	Port size	A	B
AMD150	1/8, 1/4, 3/8	239	80
AMD250	1/4, 3/8	252	80
	1/2	258	
AMD350	3/8, 1/2	284	80
	3/4	290	
AMD450	1/2, 3/4	305	80
	1	312	
AMD550	3/4, 1	339	80
AMD650	1, 1 1/2	391	80
AMD850	1 1/2, 2	540.5	80

### Precaution

Please refer to p.4.4-7 for with pressure differential gauge (GD40-2-01).

HA

ID

AMG

AFF

AM

FQ1

Related products