

# Plug-in/Plug Lead Single Unit


### Model


					size			Flow cha	racteristics			Res	sponse time (	ms)	
Series	Cor	onfiguration	Model		<b>+</b>	1 →	$1 \rightarrow 4/2 \ (P \rightarrow A/B)$		$4/2 \rightarrow 5/3 \text{ (A/B} \rightarrow \text{EA/EB)}$		Standard	Low wattage	AC	Weight (kg)	
					Pol	C [dm³/(s•bar)]	b	Cv	C [dm³/(s•bar)]	b	Cv	1 W	0.5 W	AC	(1.9)
	اے	Single	Metal seal	VQ4150		6.2	0.19	1.5	6.9	0.17	1.7	20 or less	22 or less	22 or less	0.23
	2 position	Sirigle	Rubber seal	VQ41 <sub>5</sub> 1		7.2	0.43	2.1	7.3	0.38	2.0	25 or less	27 or less	27 or less	(0.29)
_	sod	Double	Metal seal	VQ42 <sub>5</sub> 0	_	6.2	0.19	1.5	6.9	0.17	1.7	12 or less	14 or less	14 or less	0.26
			Rubber seal	VQ42 <sub>5</sub> 1		7.2	0.43	2.1	7.3	0.38	2.0	15 or less	17 or less	17 or less	(0.32)
		Closed center	Metal seal	VQ43 <sub>5</sub> 0	43°1 44°0 Rc 3/8	5.9	0.23	1.5	6.3	0.18	1.6	45 or less	47 or less	47 or less	0.28
VQ4000			Rubber seal	VQ43 <sub>5</sub> 1		7.0	0.34	1.9	6.4	0.42	1.9	50 or less	52 or less	52 or less	(0.34)
VQ4000		Exhaust	Metal seal	VQ44 <sub>5</sub> 0		6.2	0.18	1.5	6.9	0.17	1.7	45 or less	47 or less	47 or less	0.28
	tion	center	Rubber seal	VQ44 <sub>5</sub> 1		7.0	0.38	1.9	7.3	0.38	2.0	50 or less	52 or less	52 or less	(0.34)
	3 position	Pressure	Metal seal	VQ45 <sub>5</sub> 0		6.2	0.18	1.6	6.4	0.18	1.6	45 or less	47 or less	47 or less	0.28
	က	center	Rubber seal	VQ45 <sub>5</sub> 1		7.0	0.38	1.9	7.1	0.38	2.0	50 or less	52 or less	52 or less	(0.34)
		Double check	Metal seal	VQ46 <sub>5</sub> 0		2.7	_	_	3.7	_	_	55 or less	57 or les	57 or les	0.50
			Rubber seal	VQ46 <sub>5</sub> 1		2.8	_	_	3.9	_	_	62 or less	64 or less	64 or less	(0.56)





## JIS Symbol






Note 2) Based on JIS B 8375-1981 Supply pressure: 0.5 MPa, with indicator light and surge voltage suppressor, clean air. This will change depending on pressure and air quality.) The value when ON for the double type.

Note 3) Values inside () indicate the weight of plug lead units.

Table: Without sub-plate, With sub-plate: Add 0.41 kg for plug-in type, 0.30 kg for plug lead type.

## Standard Specifications

	Valve construction		Metal seal	Rubber seal			
	Fluid		Air/Inert gas	Air/Inert gas			
	Maximum operating	pressure <sup>(3)</sup>	1.0 MPa (0.7 MPa)				
ons		Single	0.15 MPa	0.20 MPa			
cati	Min. operating pressure	Double	0.15 MPa	0.15 MPa			
ecifi	procedio	3 position	0.15 MPa	0.20 MPa			
Valve specifications	Ambient and fluid ter	nperature	-10 to 50°C <sup>(1)</sup>	−5 to 50°C <sup>(1)</sup>			
/alv	Lubrication		Not required				
	Manual override		Push type/Locking type (Tool required) Option				
	Shock/Vibration resis	stance	150/30 m/s <sup>2</sup>				
	Enclosure		Dust tight (IP68	5 compatible)			
	Coil rated voltage		12, 24 VDC, 100, 110, 200, 220 VAC (50/60 Hz)				
ons	Allowable voltage flu	ctuation	±10% of rated voltage				
cati	Coil insulation type		Class B or equivalent				
ecifi		24 VDC	1 W DC (42 mA), 0	.5 W DC (21 mA)			
ds p		12 VDC	1 W DC (83 mA), 0	.5 W DC (42 mA)			
jor	Power consumption	100 VAC	Inrush 1.2 VA (12 mA), F	Holding 1.2 VA (12 mA)			
Solenoid specifications	(Current)	110 VAC	Inrush 1.3 VA (11.7 mA), F	Holding 1.3 VA (11.7 mA)			
		200 VAC	Inrush 2.4 VA (12 mA), F	Holding 2.4 VA (12 mA)			
		220 VAC	Inrush 2.6 VA (11.7 mA), Holding 2.6 VA (11				



e: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz.

Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature.

(Values at the initial period)

Note 3) Values inside ( ) denote the low wattage (0.5 W) specifications.




VQ<sub>0</sub>

VQ5

**VQZ** 

**VQD** 


## **How to Order Valves**




## **Plug-in Type**

## **Conduit terminal**

## 2 position single: VQ410<sup>0</sup><sub>1</sub>-□




## **Bottom ported drawing**




2 position double: VQ420 1-

3 position closed center: VQ430 <sup>0</sup><sub>1</sub>-□ 3 position exhaust center: VQ440 <sup>0</sup><sub>1</sub>-□

3 position pressure center: VQ450 ¹-□




## 3 position double check: VQ460 0-□



: 3 position (): Rc 3/8

# Series VQ4000 Base Mounted Plug-in Unit



G Rockwell Automation: Allen Bradley Remote I/O (RIO) System

SQ

VQ0

VQ4

VQ5

**VQZ** 

VQD

## Plug-in Unit Series VQ4000

## **Manifold Specifications**

				Porting specification	ations	Maximum	Applicable	5 station weight (kg)	
Series	Base model	Type of connection	4(A), 2(B)	Port siz	ze Note)	applicable	solenoid		
			port location	1(P), 5(R1), 3(R2)	4(A), 2(B)	stations	valve		
VQ4000	VV5Q41-□□□	■ F kit-D-sub connector ■ T kit-Terminal block box ■ L kit-Lead wire ■ S kit-Serial transmission		Rc 1/2 Option Direct exhaust with	C8 (For Ø8) C10 (For Ø10) C12 (For Ø12) Rc 1/4 Rc 3/8	F, T kit 12 stations L kit 16 stations	VQ4□00 VQ4□01	2.24 • L kit • Except solenoid valve weight	
			Bottom	silencer box	Rc 1/4	S kit 10 stations			

Note) For details about inch-size One-touch fittings and other thread standards, refer to page 2-5-39.

## Flow Characteristics at the Number of Manifold Stations (Operated individually)


Model	Passage/St	tations	Station 1	Station 5	Station 10	Station 15		
		C [dm³/(s·bar)]	5.9	5.9	5.9	5.9		
2 position metal seal	$1 \rightarrow 4/2 \ (P \rightarrow A/B)$	b	0.23	0.23	0.23	0.23		
VQ4 <sup>1</sup> <sub>2</sub> 00	, ,	Cv	1.5	1.5	1.5	1.5		
VQ4 <sub>2</sub> 00		C [dm³/(s·bar)]	6.2	6.2	6.2	6.2		
	4/2 → 5/3 (A/B → EA/EB)	b	0.19	0.19	0.19	0.19		
	,	Cv	1.5	1.5	1.5	1.5		
		C [dm³/(s·bar)]		6.8	6.8	6.8		
	1 → 4/2 (P → A/B)	b	0.31	0.31	0.31	0.31		
0	, ,	Cv	1.8	1.8	1.8	1.8		
2 position rubber seal		C [dm³/(s·bar)]	7.0	7.0	7.0	7.0		
VQ4 <sup>1</sup> <sub>2</sub> 01	4/2 → 5/3 (A/B → EA/EB)	b	0.38	0.38	0.38	0.38		
	, , , , , , , , , , , , , , , , , , , ,	Cv	1.9	1.9	1.9	1.9		





Note) Port size: Rc 3/8

Blanking plate assembly


## **Manifold Option**








## Individual EXH spacer VVQ4000-R-1-02




- Refer to pages 2-5-34 to 2-5-38
- for detailed dimensions of each option. For replacement parts, refer to page 2-5-47.
- Refer to pages 2-5-40 to 2-5-43 for control unit.




Release valve spacer


VVQ4000-24A-1D (1, 2)




SUP stop valve spacer




VVQ4000-37A-1




Double check spacer with residual pressure exhaust VVQ4000-25A-1 (1)




SUP/EXH block plate




Direct exhaust with silencer box



Interface regulator ARBQ4000-00-



For exhaust cleaner mounting [-C <sup>D</sup><sub>U</sub> ]<sup>(1)</sup>



Note 1) Release valve spacer, built-in silencer (direct exhaust), exhaust cleaner mounting and double check spacer for residual pressure exhaust cannot be combined with external pilot.

Note 2) Can be mounted on L kit only. For other kits, order E type control unit. (Refer to pages 2-5-40 to 2-5-43.)



# Kit (D-sub connector kit)

- Simplification and labor savings for wiring work can be achieved by using a D-sub connector for the electrical connection.
- Using connector for flat ribbon cable (25P) conforming to MIL standard permits the use of connectors put on the market and gives a wide interchangeability.
- Connector entry can be selected on either the U side or the D side according to the mounting orientation.
- Maximum stations are 18.

## **Manifold Specifications**

	Por	ting specifica			
Series	4(A), 2(B) port	Po	rt size	Applicable stations	
	location		4(A), 2(B)		
VQ4000	Side	Rc 1/2	C 8, 10, 12 Rc 1/4, 3/8	Max. 18 stations	
	Bottom		Rc 1/4		

## **D-Sub Connector Kit (25 pins)**

## AXT100-DS25-030 050

D-sub connector cable assemblies can be ordered by with manifolds. Refer to How to Order Manifold.

## Multi-core vinyl cable 0.3 mm<sup>2</sup> x 25C ≅ø10 4 SMC 2-M2.6 x 0.45 Socket side Terminal no.

### **D-sub Connector Cable** Assembly (Option)

Cable length (L)	Assembly part no.	Note		
1.5 m	AXT100-DS25-015	0-61-05		
3 m	AXT100-DS25-030	Cable 25 cores		
5 m	AXT100-DS25-050	X ZHAWG		

\* For other commercial connectors, use a 25 pins type with female connector conforming to MIL-C-24308.

#### Connector manufacturers' example

- Fujitsu, Ltd.
- Japan Aviation Electronics Industry, Ltd.
- J.S.T. Mfg. Co., Ltd.
- Hirose Electric Co., Ltd.

Note) As an option, the maximum number of stations can be increased by special wiring specifications.

For details, refer to page 2-5-11.

## **Electric** Characteristics

Item	Characteristics
Conductor resistance Ω/km, 20°C	65 or less
Voltage limit VAC, 1 min.	1000
Insulation resistance MΩkm, 20°C	5 or less


Note) The minimum bending radius for D-sub connector cables is 20 mm.

## **D-sub Connector Cable Assembly Terminal No.**


Cable assembly •

Lead wire color	Dot marking
Black	None
Brown	None
Red	None
Orange	None
Yellow	None
Pink	None
Blue	None
Purple	White
Gray	Black
White	Black
White	Red
Yellow	Red
Orange	Red
Yellow	Black
Pink	Black
Blue	White
Purple	None
Gray	None
Orange	Black
Red	White
Brown	White
Pink	Red
Gray	Red
Black	White
	Brown Red Orange Yellow Pink Blue Purple Gray White White Yellow Orange Yellow Pink Blue Purple Gray Orange Red Brown Pink Gray


## **How to Order Manifold**



## Electrical wiring specifications



Stations are counted starting from the first station on the D side.



## **Special Wiring Specifications**

Double wiring (connected to SOL. A and SOL. B) is used for the internal wiring of each station regardless of valve and option types. Mixed single and double wiring is available as an option.

#### 1. How to order

Indicate option symbol "-K" in the manifold part number and be sure to specify station positions for single or double wiring on the manifold specification sheet.


## 2. Wiring specifications

interface is not possible.


Note 3) When two or more symbols are specified, indicate them alphabetically.


Connections begin with the A side solenoid of the first station being connected to terminal no. 1, and continue in the order indicated by the arrows in the drawing without skipping any terminals.

Maximum stations are 18.



D-sub connector






How to Order Manifold Assembly

Specify the part numbers for valves and options together beneath the manifold base part number.

VV5Q41-05C8FD2....1 set - Manifold base part no.

D-sub connector kit with cable (3 m)



VQC

SQ VQ0

VQ4


VQ5

VO7


VQZ

VQD

# Kit (D-sub connector kit)




## **Bottom ported drawing**



<b>Dimensions</b> Formula L1 = 25n + 63, L2 = 25n + 76							n: S	Station	(Maxin	num st	andard	d 18 st	ations)					
L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
L <sub>1</sub>	88	113	138	163	188	213	238	263	288	313	338	363	388	413	438	463	488	513
L2	101	126	151	176	201	226	251	276	301	326	351	376	401	426	451	476	501	526

# Kit (Terminal block box kit)



**IP65** compliant

- Enclosure IP65 compliant
- This type has a small terminal block inside a junction box.
   The provision of a G 3/4 electrical entry allows connection of conduit fittings.
- Maximum stations are 18.
- 2 stations are used for terminal box mounting.


## **Manifold Specifications**

	Р	orting specific				
Series	4(A), 2(B)	Port s	size	Applicable stations		
	port location 1(P), 5(		4(A), 2(B)			
VQ4000	Side	Rc 1/2	C 8, 10, 12 Rc 1/4, 3/8	Max. 18 stations		
	Bottom		Rc 1/4			

## **Terminal Block Connections**

## Step 1. How to remove terminal block cover

Loosen the 4 mounting screws (M4) and open the terminal block cover.



## Step 3. How to attach the terminal block cover


Securely tighten the screws with the torque shown in thetable below, after confirming that the gasket is installed correctly.

Proper tightening torque (N·m)

0.7 to 1.2


Step 2. The diagram on the right shows the terminal block wiring. All stations are provided with double wiring regardless of the valves which are mounted.

Connect each wire to the power supply side, according to the markings provided inside the terminal block.



Applicable terminal 1.25-3S, 1.25Y-3, 1.25Y-3N, 1.25Y-3.5

## **How to Order Manifold**



SQ


VQ0

VQ4

VQ5


VQZ

VQD



Stations are counted starting from the first station on the D side.

## Electrical wiring specifications



## **Special Wiring Specifications**


Double wiring (connected to SOL. A and SOL. B) is used for the internal wiring of each station regardless of valve and option types. The optional specification permits mixture of single and double wiring. However, the maximum number of stations is 16.

#### 1. How to Order


Indicate option symbol "-K" in the manifold part number and be sure to specify station positions for single or double wiring on the manifold specification sheet.

#### 2. Wiring specifications

Connections begin with the A side solenoid of the first station being connected to terminal no. 1, and continue in the order indicated by the arrowsin the drawing without skipping any terminals.



## **How to Order Valves**



Nil	Standard type (1 W)							
Y (1)	Low wattage type (0.5 W)							
R (2) External pilot								
Note 1) Applicable to DC specifications.  Note 2) Refer to page 2-5-39 for external								

pilot specification. Combination of external pilot and perfect interface is not possible.

Note 3) When two or more symbols are specified. indicate alphabetically


## **How to Order Manifold Assembly**

Specify the part numbers for valves and options together beneath the manifold base part number.

#### <Example> Terminal block box kit

VV5Q41-07C8T0....1 set —Manifold base part no. \*VQ4100-5----2 sets —Valve part no. (Stations 1 and 2) \*VQ4200-5----2 sets -Valve part no. (Stations 3 and 4) \*VQ4300-5.....1 set —Valve part no. (Station 5) Prefix the asterisk to the part nos. of the solenoid valve, etc.

Enter in order starting from the first station on the D side. When entry of part numbers becomes complicated, indicate in the manifold specification sheet.





2

3

4

5

6


200 VAC (50/60 Hz)

110 VAC (50/60 Hz)

220 VAC (50/60 Hz)

**24 VDC** 12 VDC

## Kit (Terminal block box kit)



Note) Shown VV5Q41-08C12TO-W

SQ

VQ0


VQ4

VQ5

**VQZ** 

**VQD** 

## **Bottom ported drawing**




Formula L1 = 25n + 63, L2 = 25n + 76 n: Station (Maximum standard 18 stations) \* Including 2 stations for terminal box.

imen	sion	S		
_ 	3	4	5	6

L	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
L1	138	163	188	213	238	263	288	313	338	363	388	413	438	463	488	513
L2	151	176	201	226	251	276	301	326	351	376	401	426	451	476	501	526






**IP65** compliant


- Enclosure IP65 compliant
- Direct electrical entry. Models with two or more stations are available.
- Electrical entry can be selected on either the U side or the D side according to the mounting orientation.
- Maximum stations are 16.


## **Manifold Specifications**


Series	Po	rting specific				
	4(A), 2(B)	Poi	rt size	Applicable stations		
	port location	1(P), 5(R1), 3(R2)	4(A), 2(B)			
VQ4000	Side	Rc 1/2	C 8, 10, 12 Rc 1/4, 3/8	Max. 16 stations		
	Bottom		Rc 1/4			

## Wiring Specifications









## **How to Order Manifold Assembly**

Specify the part numbers for valves and options together beneath the manifold base part number.

## <Example> Lead wire kit with cable (3 m)

VV5Q41-05C8LD2.... 1 set —Manifold base part no.


\*VQ4100-5.....2 sets —Valve part no. (Stations 1 and 2)

\*VQ4200-5........... 2 sets —Valve part no. (Stations 3 and 4)

\*VQ4300-5............ 1 set —Valve part no. (Station 5)


Prefix the asterisk to the part nos. of the solenoid valve, etc.

Enter in order starting from the first station on the D side. When entry of part numbers becomes complicated, indicate in the manifold specification sheet.




external pilot and perfect interface is not possible. Note 3) When two or more symbols are specified, indicate them alphabetically.

# Kit (Lead wire cable)



## **Bottom ported drawing**



<b>Dimensions</b> Formula L1 = 25n + 63, L2 = 25n + 76 n: Station (Maximum 16										16 sta	itions)					
L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L <sub>1</sub>	88	113	138	163	188	213	238	263	288	313	338	363	388	413	438	463
L2	101	126	151	176	201	226	251	276	301	326	351	376	401	426	451	476

**VQC** 

VO

ī				
ı				
ı	١V	r	١.	И
ı	N۷	v	ч	4

	-	_
١,	"	h
v		

V07	
٧ŲZ	


VQZ

VQD

# S Kit (Serial transmission unit)

## IP65 compliant

- The serial transmission system reduces wiring work, while minimizing wiring and saving space.
- ●The system comes in an type SA (generic for small scale systems) for equipment with a small number of I/O points, or 32 points max., type SB (applicable to Mitsubishi Electric models) for controlling 512 I/O points max., type SC (applicable to OMRON models), type SD (applicable to SHARP models; 504 points max.), and type SF (applicable to NKE Uni-wire System; 128 points max.), type SJ (applicable to SUNX models), type SK (applicable to Fuji Electric models), type SQ (applicable to OMRON CompoBus/D), type SR (CompoBus/S).
- Maximum stations are 18.
- 2 stations are used for serial unit mounting.



- Stations are counted from station 1 on the D side.
- Double wiring (connected to SOL. A and SOL. B) is adopted for the internal wiring of each station, regardless of valve and option types.

Item	Specifications
External power supply	24 VDC +10%, -5%
Current consumption (Internal unit)	SA, SB, SBB, SD, SF, SH, SJ, SK, SQ, SR, SV: 0.1A SC: 0.3A

## **Manifold Specifications**

Series	F					
	4(A), 2(B) port	Port	Applicable stations			
	port location	1(P), 5(R1), 3(R2)	4(A), 2(B)			
VQ4000	Side	Rc 1/2	C 8, 10, 12 Rc 1/4, 3/8	Max. 18 stations		
	Bottom		Rc 1/4			

#### Type SA Type SB With general type SI unit Mitsubishi Electric Corporation (Series EX300) MELSECNET/MINI-S3 Data Link System Name of terminal block (LED M RUN M TRI LED LFD Description Description TRD Lighting during data reception **POWER** Lighting when power is turned ON Blinking when received data is normal; Lighting when data transmission **RUN/ERR** RUN Lighting when data reception with the master station is normal RD Lighting during data reception SD Lighting during data transmission ighting when reception data error occurs. FRR Light turns off when the error is corrected. • T unit Master station Can be connected with PLC I/O card for PLC made by Mitsubishi Electric Corporation serial transmission. Series MELSEC-A EX300-TMB1.....For models of Mitsubishi AJ71PT32-S3, AJ71T32-S3 **Electric Corporation** A1SJ71PT32-S3 Note EX300-TTA1.....For OMRON Max. 64 stations, connected to remote I/O EX300-TFU1.....For Fuji Electric stations (Max. 512 points). EX300-T001.....General purpose No. of output points, 16 points. No. of stations \* T units have 32 control points per unit occupied, 2 stations • No. of output points, 16 points


#### **How to Order Manifold** 08 C8 VV5Q Option Symbol Option Series • Nil None SI unit mounting position VQ4000 CD (2) Exhaust cleaner: D side mounting Nil U side mounting CU (2) Exhaust cleaner for Rc 1: U side exhaust Manifold • D D side mounting Special wiring specifications (Except double wiring) Plug-in unit Model • SD (2) Direct exhaust with silencer box: D side exhaust SU (2) Direct exhaust with silencer box: U side exhaust Without SI unit 0 **W** (2) Stations • IP65 enclosure Α With general type SI unit (Series EX300) 03 3 stations Mitsubishi Electric Corp.: MELSECNET/MINI-S3 Data Link System Note 1) When two or more symbols are specified, В indicate them alphabetically Example) -CDK Mitsubishi Electric Corp.: MELSECNET/MINI-S3 18 18 stations Note 2) Combination of [CD] and [SD] is not RR Data Link System (2 power supply systems) Note) Add 2 stations possible. OMRON Corp.: SYSBUS Wire System С for serial unit Note 3) Specify the wiring specifications in the D SHARP Corp.: Satellite I/O Link System manifold specification sheet. mounting. Note 4) Refer to pages 2-5-40 to 2-5-43 for with F1 NKE Corp.: Uni-wire System (16 output points) control unit.consumption of AC type. н NKE Corp.: Uni-wire H System Note 5) The release valve and the pressure switch Cylinder ports SUNX Corp.: S-LINK System (16 output points) J1 on the manifold with control unit are SUNX Corp.: S-LINK System (8 output points) J2 connected to another power supply. C8 With One-touch fitting for ø8 Κ Fuji Electric Co.: T-LINK Mini System Cable length is 0.6 m for L kit. C10 With One-touch fitting for Ø10 Q DeviceNet, CompoBus/D (OMRON Corp.) C12 With One-touch fitting for Ø12 R1 OMRON Corp.: CompoBus/S System (16 output points) 02 Rc 1/4 OMRON Corp.: CompoBus/S System (8 output points) R2 03 Rc 3/8 ٧ Mitsubishi Electric Corp.: CC-LINK System В Bottom ported Rc 1/4 G Rockwell Automation: Allen Bradley Remote I/O (RIO) System CM Mixed U JEMANET (JPCN-1)

<sup>\*</sup> For details on specifications and handling, refer to the separate technical instruction manual.

## • Correspondence of SI unit output numbers and solenoid valve coils

Mixed wiring is available as an option. Use the manifold specification sheet to specify.

<Wiring example 1> Double wiring (Standard)



<Wiring example 2> Single/Double mixed wiring (Option) Double Double Double Double Double Single Single Slunit SI unit output no. ∀ B

VQC

U side

SQ

VQ0

VQ4

VQ5

VQZ

VQD

N O Type SD Type SC **OMRON** Corporation SHARP Corporation SYSBUS Wire System Satellite I/O Link System Name of terminal block (LED) LED LED Description Description POWER ON when power supply is ON Lights when transmission is normal RUN and PLC is in operation mode Lights when power is ON and slave RUN stations are operating normally T/R Blinks during data transmission/reception ERR ON when transmission is abnormal. Lights when slave station switch setting **ERROR** is abnormal, communication is abnormal, PLC stopped and defective slave unit R.SET ON for master unit control input HOLD Master station unit Master station unit SHARP Corporation PLC **OMRON PLC** New Satellite Series W SYSMAC C(CV) series ZW-31LM Types C500-RM201 and C200H-RM201 New Satellite Series JW \* 32 units max., transmission terminal JW-23LM, JW-31LM connection (512 points max.) Max. 31 units, I/O slave stations connected • No. of output points, 16 points (504 points max.) • No. of output points, 16 points

## Series d **Enclosure**


VQ4000 Type of actuation •

1	2 position single
2	2 position double
3	3 position closed center
4	3 position exhaust center
5	3 position pressure center
6	3 position double check

**How to Order Valves** 

## Seal

0	Metal seal
1	Rubber seal



Nil

w

Manual override

Dusttight

Dusttight/Low jetproof type

(IP65)

Y (1) Low wattage type (0.5 W) **R** (2) External pilot

Note 1) Applicable to DC specifications. Note 2) For external pilot specifications, refer to page 2-5-39.


Combination of the external pilot and perfect interface is not possible.

Note 3) When two or more symbols are specified, indicate them alphabetically.

## **How to Order Manifold Assembly**


Specify the part numbers for valves and options together beneath the manifold base part number.

#### <Example> Serial transmission unit




When entry of part numbers becomes complicated,

indicate in the manifold specification sheet.



# S Kit (Serial transmission unit)



Note) In the case of EX124 for SI unit, conduit port (G 1/2) will be 4 locations.

Formula L1 = 25n + 63, L2 = 25n + 76 n: Station (Maximum standard 18 stations)

\* Including 2 stations for mounting SI unit box.

	molecuming 2 statutorio for moduluming of clima															
L	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
L <sub>1</sub>	138	163	188	213	238	263	288	313	338	363	388	413	438	463	488	513
L2	151	176	201	226	251	276	301	326	351	376	401	426	451	476	501	526

Note) Shown VV5Q41-08C12SQ-W



**Dimensions** 



SQ


VQ0

VQ4

VQ5

**VQZ** 

**VQD** 



Formula L1 = 25n + 63, L2 = 25n + 76 n: Station (Maximum standard 18 stations)

Dimen	<ul> <li>Including 2 stations for mounting SI unit box.</li> </ul>															
L	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
L1	138	163	188	213	238	263	288	313	338	363	388	413	438	463	488	513
La	151	176	201	226	251	276	201	226	251	276	401	126	151	176	501	526

# S

## Kit (Serial transmission kit) for I/O

**IP65** compliant

## Applicable network: DeviceNet/PROFIBUS-DP

• The serial transmission system reduces wiring work, while minimizing wiring and saving-space.


## SI unit for DeviceNet/PROFIBUS

## Input block

As a slave for DeviceNet/PROFIBUS, it is possible to control ON/OFF of a solenoid valve with the maximum of 32 points. Furthermore, by connecting a discrete input block, it is possible to input the sensor signal for 32 points at the maximum.

Meaning of an expansion block, connecting with SI unit, for sensor-inputting for auto switches, etc. Sensor-input is available up to 8 per one input block. By the NPN/PNP switch, it is able to adjust COM to sensor.

## **Details in Connector**



## Communication connector (PROFIBUS-DP): Made by CONINVERS GmbH RC-2RS1N12 12 pins


Cable side connector example: Made by Siemens AG 6ES5 760-2CB11



Number	Description	Function							
1	M5V	GND Terminal							
2	Α	Signal-N							
4	В	Signal-P							
6	+5V	Terminal + 5V							
9	SIELD	Shield ground							
12	RTS	Optical fiber (Reserve)							

Pin no. 3, 5, 7, 8, 10 and 11 marked with ● are open.

 $\ast$  Connector's shape and pin assignment is interchangeable with ET200C made by Siemens AG.



## SI unit COM

With I	With no SI/Input unit (For SDOW)								
+COM	DeviceNet (SDQW)								
-COM	Profibus DP (SDNWN)								
	+COM	+COM DeviceNet (SDQW)							

Note) Only +COM is available for DeviceNet. Order a mounting valve with +COM.
Since PROFIBUS is -COM only, order -COM

for valves to be mounted.



SQ

VQ0

VQ4

VQ5

VQZ

VQD

### **Details in Connector**

### Input connector: M12 5 pins (XS2F compatible made by OMRON Corp.) x 8 pcs.

Cable side connector example: XS2G made by OMRON Corp.



	Number	Description	Function
	1	SW+	Sensor power supply +
	2	N.C.	Open*
}	3	SW-	Sensor power supply –
	4	SIGNAL	Sensor input signal
	5	PE	Protective sensor ground

\* No. 2 pin of the input no. 0, 2, 4, 6 connector (connectors aligned in the right side on the input block) is connected internally with no. 4 pin (sensor input no.) of the input no. 1, 3, 5, 7 respectively. Thereby, it is possible to directly input 2 points which is bundled into 1 cable by the cluster connector, etc.

Connector in	nput no.	Input no.: 1, 3, 5,					
SW +		1		1			
SIGNAL-n + 1		2		2			
SW-		3		3			
SIGNAL-n		4		4			
PE		5		5			

## **⚠** Caution

When an enclosure equivalent to IP65 is required, place a waterproof cover on the unused input connector. As for waterproof cover, order it separately.

Example: OMRON Corp. XS2Z-12

## Power source connector: Series 723 (made by Franz Binder GmbH & Co. KG) 5 pins (72309-0115-80-05)

Cable side connector example: Franz Binder GmbH & Co. KG 72309-0114-70-15, etc.  $\ast$  DIN type 5 pins



	Number	Description	Function
	1	SV24V	For solenoid valve +24 V
2	2	SV0V	For solenoid valve 0 V
1	3	PE	Protective ground
	4	SW24V	<devicenet>For input block + 24 V, <profibus interbus="" or="">For input unit and SI unit + 24 V</profibus></devicenet>
	5	SW0V	<devicenet>For input block 0 V, <profibus interbus="" or="">For input unit and SI unit 0 V</profibus></devicenet>

## Communication connector (DeviceNet): M12 5 pins (for DeviceNet compliant)

Example of corresponding cable assemblies with connector: OMRON Corporation: DCA1-5CN05F1 Karl Lumberg GmbH & Co. KG: RKT5-56



Number	Description	Function							
1	Drain	Drain/Shield							
2	V+	Circuit power supply +							
3	V-	Circuit power supply -							
4	CAN_H	Signal H							
5	CAN_L	Signal L							

Item conforming to Micro style connector in DeviceNet specifications.

## **How to Order Manifold Assembly**

Specify the part numbers for valves and options together beneath the manifold base part number.

## <Example> Serial transmission unit

VV5Q41-05C8SDQW1-W---1 set —Manifold base part no.

\*VQ4100-5W------2 sets —Valve part no. (Stations 1 and 2)


\*VQ4200-5W------1 set —Valve part no. (Stations 3 and 4)


\*VQ4300-5W------1 set —Valve part no. (Station 5)

Prefix the asterisk to the part nos. of the solenoid valve, etc.

Enter in order starting from the first station

Enter in order starting from the first station on the D side. When entry of part numbers becomes complicated, indicate in the manifold specification sheet.





Note 1) Applicable to DC specifications. Note 2) For external pilot specifications, refer to page 2-5-39.


Note 3) When two or more symbols are specified, indicate them alphabetically.

possible.

Combination of the external pilot and perfect interface is not

# S

## Kit (Serial transmission unit) for I/O




**Dimensions** 

Formula L1 = 25n + 63, L2 = 25n + 198 Stations \* In the case of DI unit, 1 pc., 54 mm is added per 1 pc.

Dillicit	31011	3		11.	ii. Stations * iii the case of bi unit, 1 pc., 54 min is added per 1 pc.										
_ n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	113	138	163	188	213	238	263	288	313	338	363	388	413	438	463
L2	248	273	298	323	348	373	398	423	448	473	498	523	548	573	598


## Indicator Unit (LED) Descriptions and Functions

## ■ SI Unit (DeviceNet)




Description	Function							
PWR(V)	ON when solenoid valve power supply is turned ON							
PWR	ON when DeviceNet circuit power supply input is turned ON							
	OFF: Power supply off, off line, or when checking duplication of MAC_ID							
	Green blinking: Waiting for connection (On line)							
MOD/NET	Green ON: Connection established (On line)							
	Red blinking: Connection time out (Minor communication abnormality occurs)							
	Red ON: MAC_DI duplication error, or BUSOFF error							
	(Major communication abnormality occurs)							

## ■ SI Unit (PROFIBUS-DP)



Description	Function
PWR	ON when solenoid valve power supply is turned ON OFF when the power supply voltage is less than 19 V
RUN	ON when operating (SI unit power supply is ON)
DIA	ON when self-diagnosis device detects abnormality
BF	ON for BUS abnormality

## ■ Input block



Description	Function
PWR	ON when sensor power is turned ON OFF when short circuit protection is working
0 to 7	ON when each sensor input goes ON

SQ


VQ0

VQ4

VQ5

**VQZ** 

**VQD** 




Formula L1 = 25n + 63, L2 = 25n + 252n: Stations

Dimens	sion	S			* In the case of 2 pcs. DI unit, 105 mm will be added per 2 pcs.										
L n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	113	138	163	188	213	238	263	288	313	338	363	388	413	438	463
L2	302	327	352	377	402	427	452	477	502	527	552	577	602	627	652

## Construction

## **Plug-in Unit**





## **Component Parts**


Number	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool/Sleeve	Stainless steel	
3	Piston	Resin	

## **Replacement Parts**

4	Pilot valve assembly	VQZ111P-□	*: Coil rated voltage Example) 24 VDC: 5
---	----------------------	-----------	---







## **Component Parts**

Number	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool valve	Aluminum, NBR	
3	Piston	Resin	

## **Replacement Parts**

